

IPX5 IPX6 IPX7 Rain Test Machine / Stabilized Waterproof Test Equipment

Basic Information

- Place of Origin:
- Brand Name:
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Payment Terms:
- Supply Ability:



Product Specification

- Goods Name:
- Rated Power:
- Observation Window:
- 2.0 Kw Tempered Glass (thickness: 12mm)

IPX7 Rain Test Machine

Guangdong, China

usd+20000-50000+pcs

wooden box package

ISO20653:2013 IEC60529:2013 IEC60598:2021 DIN40050-9:1993

YueXin

IPX57AT

30-45 days

100+pcs+30

380V/50HZ

50KG

1 pcs

T/T

- Power Supply:
- Turn Table Load Bearing:
- Turn Table Lifting Height: Non-lifting (Fixed)
- Highlight:
- IPX5 Rain Test Machine, IPX7 Rain Test Machine, IPX6 Rain Testing Machine

Stabilized IPX5-7 Waterproof Test Machine

Product characteristics:

- 1, This machine is suitable for IPX5, IPX6, IPX7 waterproof test.
- 2, The fuselage is made of 304 stainless steel to ensure that it will not rust for the long-term test.
- 3, The size of the water storage tank is: 1000-800-1200mm(compatible with IPX7 test chamber).
- 4, The highest water level of IPX7 is 1.2 meters; there is a lifting device on the top of the immersion tank, which is convenient for taking and placing samples.
- 5, Use flowmeter to adjust flow rate to meet standard requirements: 12.5L/min±5%(IPX5) 100L/min±5%(IPX6).
- 6, The speed of the turntable is adjustable, and the adjustment range is 1-5R/min.
- 7, The turntable is equipped with a sample power socket, which can provide an electrified test environment for the sample.
- 8, The bottom is installed with brake casters which is convenient for users to move and fix.

9, The equipment is equipped with a special spray gun holder to reduce the pressure of hand-held operation and make the test more convenient. 10, The observation window is made of 12mm tempered glass (W200mm×H1100mm), which can clearly observe the test situation of the sample.

Usage:

This machine is mainly used to test the waterproof level of the shell of lamps, household appliances, electronic products, etc. by simulating the environmental conditions such as water spraying, heavy spraying, immersion. After the test, check and determine whether the waterproof level of the product shell meets the requirements, so as to facilitate enterprises to improve product design and factory inspection.

Technical parameter:

| External dimensions | W1100×D900×H2400mm |
|--------------------------------|---|
| Turntable size | W600×D600×H600mm |
| Storage tank volume | 960L,W1000×D800×H1200mm |
| Turn table diameter | Ø600mm |
| IPX5 nozzle diameter | Ø6.3mm |
| IPX6 nozzle diameter | Ø12.5mm |
| Water Flow(IPX5) | 12.5±0.625(L/min) |
| Water Flow(IPX6) | 100±5(L/min) |
| Water flow control | Manually adjust by flowmeter |
| Water spray distance | 2.5-3m(Controlled by the operator) |
| nozzle fixed way | Fixed by a special bracket |
| Turn table load bearing | 50kg |
| Turn table lifting height | Non-lifting (Fixed) |
| Water spraying mode | Disposable water spray, can not be recycled |
| observation window | Tempered glass (thickness: 12mm) |
| Observation window width | 200mm |
| Water level adjustment method | Inlet/drain valve, manual adjustment |
| Load bearing of lifting device | 100kg |
| Control system | (Touch) 7 "touch screen +PLC |
| Power supply | 380V/50HZ |
| Sample power supply | 220V/10A |
| Rated Power | 2.0 kw |

Installation and use conditions:

1, Site of installation : Recommended installation position dimensions≥W3500×D2500×H2500mm

2, Power supply: 380V / 50HZ (This is negotiable and adapted to customer conditions), and the length of the power cable is 2.5 m;

3, Water source requirement : The supplier delivers 6 meters water pipe (specification DN15), and the user needs to ensure that the water source is within this range (if it needs to be extended, please explain in advance);

4, Drainage requirement: Users should make drainage channels in the site in advance.

Accessories list:

Operating instruction /1pcs Data CD/USB disk /1pcs(May need to be sent separately according to the actual situation)

Notice:

Due to the technical upgrade, some technical parameters do not conform to the actual machine, please forgive us without further notice.

Detail picture:

