

# 1000L Sand Dust Test Chamber 220V 380V With Digtal Flow Meter

IEC60529:2013, DIN EN 60529-1:2014-09

# **Basic Information**

- Place of Origin:
- Brand Name: YueXin

Guangdong, China

(VDE 0470-1)

1 pcs

T/T

2

Talcum

30-45 days

100+pcs+30

YX-IP56XS-1000L

usd+20000-50000+pcs

wooden box package

- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Payment Terms:
- Supply Ability:



# **Product Specification**

- Goods Name:
- Material Of Window: Tempered Glass
- Experimental Scenarios:
- Number Of Dust Outlet:
- Test Medium:
- Test Function:
- Outer Material:
- Sample Rack Load Bearing:50KG/
- Highlight:
- Steel Plate g:50KG/ 1000L Sand Dust Test Chamber, Sand Dust Test Chamber 220V,

1000L Sand And Dust Test Chamber

Sand And Dust Test Chamber

Dust Environment

IP5X IP6X IP5KX IP6KX



### More Images



### 1000L Widely Used Sand Dust Test Chamber with Digtal Flow Meter for IP5X IP6X

#### Vacuum system:

The user needs to connect the sample to a special pumping pipe, and the gas inside the sample is pumped out by a vacuum pump, and the pumping speed can be adjusted by an air flow meter. • Need to reserve the air hole position for the sample.

Equipment structure:

Designed with a compact interior and a single, conveniently placed door, this dust-proof chamber efficiently blocks out external dust particles, preserving the purity of equipment within, perfectly suited for use in space-constrained testing environments.

The talcum powder is blown to the top of the pipeline by the circulation pump and is sprayed out from the dust outlet above the inner box, and moves in disorder after falling freely.

There is a special outlet at the bottom of the funnel, user can quickly collect dust through there.

To keep the test space as dry as possible, a heater is mounted on the outside of the funnel floor.

A vibrator is mounted on the outside of the funnel, which can work intermittently to keep the dust from sticking to the inner wall as much as possible.

The pumping pressure is displayed by the pressure sensor(Unit:kPa), and can be adjusted by the pressure regulating valve; The pumping speed can be displayed by the flow sensor(Unit:slpm), and the total pumping volume and current pumping speed can be displayed.

The door is transparent and equipped with a window wiper to allow perfect observation of the test space.

The sample power socket (220V, 10A) is mounted under the side of the chassis, which is convenient for the user to do the live test of the sample<sup>6</sup>.

Controller: 7-inch touch screen + PLC, using Yuexin self-developed software, which can be switched to multiple language<sup>3</sup>. Casters are mounted to the bottom, and can be adjusted to fix the chassis according to the flatness of the ground. Protection measures: short circuit protection, blower overload protection.

#### Technical data for IP5X IP6X:

ltem	Parameter
Test space volume	1000 L
Number of dust outlet	2
Diameter of the dust outlet	50 mm
Talc Specifications	15 μm
Talc dosage	2 4 kg/m <sup>3</sup>
Outer diameter of exhaust pipe	8mm
Pumping speed	Digital display, Unable to adjust
Maximum depression	2kPa(20mbar)
Cycle test times	0-999 times
Test time	0-999 H
Vibration time	0-999 S
Sound pressure level during operation <sup>8</sup>	≤70 dB (measured at 1m in free field)
Power supply	380 V/50 HZ
Sample power <sup>9</sup>	220 V/10 A
Power	3.5 kw

#### Application:

Employed primarily for replicating arduous settings, dust-proof enclosures play a pivotal role in verifying the impermeability and dependability of products and machinery. They cater to diverse industries, including electronics, automotive, and aviation, assisting in gauging electronic devices' resistance to dust, automotive components' functionality in sandy climates, and more, ensuring products remain steadfast and secure in challenging environments.

#### Notices:

1 The pictures in this document are for customer reference only, and there may be color differences between the actual model and the pictures.

2 This document only lists some test standards, which does not mean that other test requirements and standards cannot be conducted. Welcome to communicate and discuss with us.

3 One test only at a time. The next project can be only carried out after the current test is completed. In addition, we can provide multi-functional customized test solutions according to user requirements.

4 A single device is equipped with an exhaust pipe, and only one sample is vacuumed at a time.

5 Please prepare a powder collection box (6-10L) in advance, remove the sealing plate at the bottom of the back, and then collect it.

6 Please inform in advance if the voltage(220V) does not match the actual needs so that we can provide customized solutions for you.

7 At present, only Chinese and English interfaces are supported; if other languages are introduced, the software can be updated remotely.

8 The data is collected in the manufacturer's factory test. It may be different in different environments.

for more products please visit us on raintestchambers.com

9 If the sample is not suitable for sample testing, a connection hole can be customized on the left side of the inner box, and the user can use an external power supply by himself.

10 The photos may not match the actual ones, and are for user reference only.

### The detail photos of product:



filter

Tags: Dustproof Climatic Chamber, Dustproof Environmental Chamber, IP5X IP6X Dust Testing Machine

